






	Platform	Intra Oral Scan Body	Desktop Scan Body	Model Analog	Model Analog Tool	Hybrid Base Single	Margin Width	Prosthetic screw - implant manufacturer	Screwdriver Hybrid Base Single	API® Bridge	Hybrid Base Bridge	Margin Width	Prosthetic screw - hexalobular	Prosthetic Screwdriver	Torque		
		Art No:	Art No:	Art No:	Art No:	Art No:	Size	Art No:	Art No:	Art No:	Art No:	Size	Art No:	Art No:	Ncm		
Biomet 3i® Certain	3.4	IO 7B-A	7B-A	MA-BCE34-1	AT-16-1	HB-BCE34-1	Ø 3.1	AS-BCEM168POS	0.050° (1.25 mm) Hex screwdriver			Ø					
	4.1	IO 7B-B	7B-B	MA-BCE41-1		HB-BCE41-1	Ø 3.4										
	5.0			MA-BCE50-1		HB-BCE50-1	Ø 5.0										
	6.0			MA-BCE60-1		HB-BCE60-1	Ø 6.0										
Biomet 3i® External Hex	3.4	IO 7A-A	7A-A	MA-BEH34-1	AT-20-1			AS-BEHM208POS	0.050° (1.25 mm) Hex screwdriver			Ø			32 Ncm		
	4.1	IO 7A-B	7A-B	MA-BEH41-1													
	5.0			MA-BEH50-1													
	6.0			MA-BEH60-1													
Camlog®	3.3	IO 9A-A	9A-A	MA-CAS33-1	AT-16-1			AS-CASM1610POS	1.28 mm Hex screwdriver			Ø			20 Ncm		
	3.8	IO 9A-B	9A-B	MA-CAS38-1													
	4.3	IO 9A-C	9A-C	MA-CAS43-1													
	5.0/6.0	IO9A-D	9A-D	MA-CAS50-1												AT-20-1	AS-CASM2010POS
Dentsply Ankylos®	3.5-7.0	IO 8B-A SA	8B-A	MA-DAN35/70-1	AT-16-1				1.0 mm Hex screwdriver								
Dentsply Ankylos® Balance Base	BB NP	IO 8C-A	8C-A	MA-DBA40-1	AT-16-1					HBB-DBA40-1	HBBS-DBA40-1	Ø .05	AS-DBAM1605A-1	PS-AH18-1, PS-AH26-1 or PS-AH34-1	10 Ncm		
Astra Tech Implant System™ OsseoSpeed® TX	3.0	IO 3A-A SA	3A-A	MA-ATO30-1	AT-14-1	HB-ATO30-1	Ø 3.4	AS-ATOM148POS	0.050° Hex screwdriver							15 Ncm	
	3.5/4.0	IO 3A-B SA	3A-B	MA-ATO35-1	AT-16-1	HB-ATO35/40-1	Ø 3.7	AS-ATOM168POS								20 Ncm	
	4.5/5.0	IO 3A-C SA	3A-C	MA-ATO45-1	AT-20-1	HB-ATO45/50-1	Ø 4.5	AS-ATOM2010POS								25 Ncm	
Astra Tech Implant System™ OsseoSpeed® EV	3.0	IO 3B-A SA		MA-ATE30-1	AT-14-1	HB-ATE30-1	Ø 3.5	AS-ATEM148POS	0.050° Hex screwdriver							25 Ncm	
	3.6	IO 3B-B SA		MA-ATE36-1	AT-16-1	HB-ATE36-1	Ø 3.7	AS-ATEM168POS									
	4.2	IO 3B-C SA		MA-ATE42-1	AT-18-1	HB-ATE42-1	Ø 4.5	AS-ATEM188POS									
	4.8	IO 3B-D SA		MA-ATE48-1	AT-20-1	HB-ATE48-1	Ø 4.5	AS-ATEM208POS									
	5.4	IO 3B-E SA		MA-ATE54-1		HB-ATE54-1	Ø 5.0										
Astra Tech Implant System™ OsseoSpeed® EV Profile	4.2	IO 3C-A SA		MA-ATE42P-1	AT-18-1			AS-ATEM188POS	0.050° Hex screwdriver							25 Ncm	
	4.8	IO 3C-B SA		MA-ATE48P-1	AT-20-1			AS-ATEM208POS									
Astra Tech Implant System™ EV Uni Abutment	UA33°	IO 3D-A		MA-AUE33-1	AT-18-1				0.050° Hex screwdriver	HBB-AUE33-1	HBBS-AUE33-1	Ø 5.0	AS-AUEM1805A-1	PS-AH18-1, PS-AH26-1 or PS-AH34-1	15 Ncm		
Dentsply Xive®	3.0	IO 8A-A	8A-A	MA-DX130-1	AT-14-1			AS-DXIM1409POS	1.22 mm Hex screwdriver							24 Ncm	
	3.4	IO 8A-B	8A-B	MA-DX134-1													
	3.8	IO 8A-C	8A-C	MA-DX138-1	AT-16-1												AS-DXIM1609POS
	4.5/5.5	IO 8A-D	8A-D	MA-DX145-1													
Neoss® Access		IO 1B-A	1B-A	MA-NAC40-1	AT-20-1												
Neoss® Implant System	3.25	IO 1A-B	1A-B	MA-NIS33-1	AT-16-1				Neoss Implant Insertor								
	3.5-5.5	IO 1A-A	1A-A	MA-NIS35/55-1	AT-20-1			AS-NISM207POS								32 Ncm	
Nobel Biocare® Brånemark System®	3.3/3.5 NP	IO 6A-A	6A-A	MA-BRA35-1	AT-16-1	HB-BRA35-1	Ø 4.5	AS-BRAM167POS	Nobel Biocare Unigrip	HBB-BRA35-1	HBBS-BRA35-1	Ø 5.0	AS-BRAM1607A-1	PS-AH18-1, PS-AH26-1 or PS-AH34-1	35 Ncm		
	3.75/4.0 RP	IO 6A-B	6A-B	MA-BRA41-1	AT-20-1	HB-BRA41-1	Ø 4.5	AS-BRAM207POS		HBB-BRA41-1	HBBS-BRA41-1	Ø 6.0	AS-BRAM2007A-1				
	5.0/5.5 WP	IO 6A-C	6A-C	MA-BRA51-1	AT-25-1	HB-BRA51-1	Ø 4.5	AS-BRAM257POS		HBB-BRA51-1	HBBS-BRA51-1	Ø 6.0	AS-BRAM2507A-1				
Nobel Biocare® Conical Connection	3.0	IO 2B-D / SA	2B-D	MA-NBA30-1	AT-14-1	HB-NBA30-1	Ø 3.1	AS-NBAM1407POS	Nobel Biocare Unigrip						15 Ncm		
	3.5/3.75 NP	IO 2B-A / SA	2B-A	MA-NBA35-1	AT-16-1	HB-NBA35-1	Ø 3.7	AS-NBAM168POS		HBB-NBA35-1	HBBS-NBA35-1	Ø 5.0	AS-NBAM1608A-1	PS-AH18-1, PS-AH26-1 or PS-AH34-1	35 Ncm		
	4.3/5.0 RP	IO 2B-B / SA	2B-B	MA-NBA43-1	AT-20-1	HB-NBA43-1	Ø 4.5	AS-NBAM207POS		HBB-NBA43-1	HBBS-NBA43-50-1	Ø 5.0	AS-NBAM2007A-1				
	5.5 WP	IO 2B-C / SA	2B-C	MA-NBA60-1		HB-NBA60-1	Ø 4.5			HBB-NBA60-1	HBBS-NBA60-1	Ø 5.7					
Nobel Biocare® Multi-Unit	NP/RP	IO 2C-A	2C-A	MA-MUA45-1	AT-14-1				Nobel Biocare Unigrip	HBB-MUA45-1	HBBS-MUA45-1	Ø 5.0	AS-MUAM1403A-1	PS-AH18-1, PS-AH26-1 or PS-AH34-1	15 Ncm		
	WP	IO 2C-B	2C-B	MA-MUA60-1	AT-18-1					HBB-MUA60-1	HBBS-MUA60-1	Ø 5.7	AS-MUAM1804A-1				
Nobel Replace®	3.5 NP	IO 2A-A	2A-A	MA-NBR35-1	AT-18-1	HB-NBR35-1	Ø 4.5	AS-NBRM1808POS	Nobel Biocare Unigrip							35 Ncm	
	4.3 RP	IO 2A-B	2A-B	MA-NBR43-1	AT-20-1	HB-NBR43-1	Ø 4.5	AS-NBRM2010POS									
	5.0 WP	IO 2A-C	2A-C	MA-NBR50-1		HB-NBR50-1	Ø 5.0										
	6.0	IO 2A-D	2A-D	MA-NBR60-1		HB-NBR60-1	Ø 6.0										
Straumann® Bone Level	3.3 NC	IO 4A-A SA	4A-A	MA-SBO33-1		AT-16-1	HB-SBO33-1		Ø 3.5	AS-SBOM1608POS	SCS screwdriver	HBB-SBO33-1	HBBS-SBO33-1	Ø 5.0	AS-SBOM1608A-1	PS-AH18-1, PS-AH26-1 or PS-AH34-1	35 Ncm
	4.1/4.8 RC	IO 4A-B SA	4A-B	MA-SBO41-1	HB-SBO41-1		Ø 4.1										
Straumann® Bone Level on Screw-retained Abutment	3.5	IO 4D-A		MA-SSA35-1	AT-14-1				SCS screwdriver	HBB-SSA35-1	HBBS-SSA35-1	Ø 5.0	AS-SSAM1404A-1	PS-AH18-1, PS-AH26-1 or PS-AH34-1	15 Ncm		
	4.6	IO 4D-B		MA-SSA46-1		HBB-SSA46-1	HBBS-SSA46-1	Ø 5.0									
Straumann® Standard Tissue Level	3.5 NNC	IO 4C-A	4C-A		AT-20-1				SCS screwdriver					AS-SSYM2007A-1	PS-AH18-1, PS-AH26-1 or PS-AH34-1	35 Ncm	
	4.8 RN	IO 4B-A	4B-A	MA-SSY48-1		HB-SSY48-1	Ø 4.5										
	6.5 WN	IO 4B-B		MA-SSY65-1		HB-SSY65-1	Ø 7.0										
Zimmer Screw-Vent®	3.5	IO 5A-A	5A-A	MA-ZSV35-1	AT-18-1	HB-ZSV35-1	Ø 4.5	AS-ZSVM1808POS	1.25 mm Hex screwdriver							30 Ncm	
	4.5	IO 5A-B	5A-B	MA-ZSV45-1		HB-ZSV45-1	Ø 5.0										
	5.7	IO 5A-C	5A-C	MA-ZSV57-1		HB-ZSV57-1	Ø 6.0										

Elos Medtech Library overview



Naming in 3Shape & Dental Wings	Naming in Exocad		Bridges and Bars in one-piece		Single Abutment	Single Abutment IO	Single Abutment IO SA	Hybrid Base Single	Hybrid Base Single IO	Hybrid Base Single IO SA	Hybrid Base Bridge	Hybrid Base Bridge IO	Hybrid Base Bridge IO SA
	Manufacturer	Connection	Desktop scanbody	IntraOral scanbody									
Neoss Implant system 3.5-5.5	NE	PA	1A-A	IO 1A-A	1A-A	IO 1A-A	-	-	-	-	-	-	-
Neoss Implant system 3.25	NE	PA	1A-B	IO 1A-B	1A-B	IO 1A-B	-	-	-	-	-	-	-
Neoss Access	NE	ACC	1B-A	IO 1B-A	-	-	-	-	-	-	-	-	-
Nobel Replace NP	NB	RP	2A-A	IO 2A-A	2A-A	IO 2A-A	-	2A-A	IO 2A-A	-	-	-	-
Nobel Replace RP	NB	RP	2A-B	IO 2A-B	2A-B	IO 2A-B	-	2A-B	IO 2A-B	-	-	-	-
Nobel Replace WP	NB	RP	2A-C	IO 2A-C	2A-C	IO 2A-C	-	2A-C	IO 2A-C	-	-	-	-
Nobel Replace 6.0	NB	RP	2A-D	IO 2A-D	2A-D	IO 2A-D	-	2A-D	IO 2A-D	-	-	-	-
Nobel CC 3.0	NB	AC	2B-D	IO 2B-D	2B-D	IO 2B-D	IO 2B-D SA	2B-D	IO 2B-D	IO 2B-D SA	-	-	-
Nobel CC NP	NB	AC	2B-A	IO 2B-A	2B-A	IO 2B-A	IO 2B-A SA	2B-A	IO 2B-A	IO 2B-A SA	2B-A	IO 2B-A	-
Nobel CC 4.3 RP	NB	AC	2B-B	IO 2B-B	2B-B	IO 2B-B	IO 2B-B SA	2B-B	IO 2B-B	IO 2B-B SA	2B-B	IO 2B-B	-
Nobel CC 5.0 RP	NB	AC	2B-B	IO 2B-B	2B-B	IO 2B-B	IO 2B-B SA	2B-B	IO 2B-B	IO 2B-B SA	2B-B	IO 2B-B	-
Nobel CC 6.0 WP	NB	AC	-	-	-	-	-	2B-C	IO 2B-C	-	2B-C	IO 2B-C	-
Nobel Multi Unit NP/RP	NB	Multi	2C-A	IO 2C-A	-	-	-	2C-A	IO 2C-A	-	2C-A	IO 2C-A	-
Nobel Multi Unit WP	NB	Multi	2C-B	IO 2C-B	-	-	-	2C-B	IO 2C-B	-	2C-B	IO 2C-B	-
Astra Tech 3.0	AS	OS	-	-	3A-A	-	IO 3A-A SA	3A-A	-	IO 3A-A SA	-	-	-
Astra Tech 3.5/4.0	AS	OS	-	-	3A-B	-	IO 3A-B SA	3A-B	-	IO 3A-B SA	-	-	-
Astra Tech 4.5/5.0	AS	OS	-	-	3A-C	-	IO 3A-C SA	3A-C	-	IO 3A-C SA	-	-	-
Astra Tech EV 3.0	AS	EV	-	-	-	-	IO 3B-A SA	-	-	IO 3B-A SA	-	-	-
Astra Tech EV 3.6	AS	EV	-	-	-	-	IO 3B-B SA	-	-	IO 3B-B SA	-	-	-
Astra Tech EV 4.2	AS	EV	-	-	-	-	IO 3B-C SA	-	-	IO 3B-C SA	-	-	-
Astra Tech EV 4.8	AS	EV	-	-	-	-	IO 3B-D SA	-	-	IO 3B-D SA	-	-	-
Astra Tech EV 5.4	AS	EV	-	-	-	-	IO 3B-E SA	-	-	IO 3B-E SA	-	-	-
Astra Tech EV 4.2 (Profile)	AS	EV-P	-	-	-	-	IO 3C-A SA	-	-	-	-	-	-
Astra Tech EV 4.8 (Profile)	AS	EV-P	-	-	-	-	IO 3C-B SA	-	-	-	-	-	-
Astra Tech UNI Abutment EV	AS	EV-U	-	-	-	-	-	-	-	-	-	IO 3D-A	-
Straumann Bonelevel NC 3.3	STR	BL	4A-A	-	4A-A	-	IO 4A-A SA	4A-A	-	IO 4A-A SA	4A-A	-	IO 4A-A SA
Straumann Bonelevel RC 4.1	STR	BL	4A-B	-	4A-B	-	IO 4A-B SA	4A-B	-	IO 4A-B SA	4A-B	-	IO 4A-B SA
Straumann Bonelevel RC 4.8	STR	BL	4A-B	-	4A-B	-	IO 4A-B SA	4A-B	-	IO 4A-B SA	4A-B	-	IO 4A-B SA
Straumann Standard RN	STR	SYN	4B-A	IO 4B-A	4B-A	IO 4B-A	IO 4B-A SA	4B-A	IO 4B-A	IO 4B-A SA	4B-A	IO 4B-A	-
Straumann Standard WN	STR	SYN	4B-A	IO 4B-B	4B-A	IO 4B-B	IO 4B-A SA	4B-A	IO 4B-B	IO 4B-A SA	4B-A	IO 4B-B	-
Straumann NNC	STR	NNC	4C-A	IO 4C-A	4C-A	IO 4C-A	-	-	-	-	-	-	-
Straumann Screw-retained 3.5	STR	SR	-	-	-	-	-	-	-	-	-	IO 4D-A	-
Straumann Screw-retained 4.6	STR	SR	-	-	-	-	-	-	-	-	-	IO 4D-B	-
Zimmer Screwvent 3.5	ZI	TSV	5A-A	IO 5A-A	5A-A	IO 5A-A	-	5A-A	IO 5A-A	-	-	-	-
Zimmer Screwvent 4.5	ZI	TSV	5A-A	IO 5A-B	5A-A	IO 5A-B	-	5A-A	IO 5A-B	-	-	-	-
Zimmer Screwvent 5.7	ZI	TSV	5A-B	IO 5A-C	5A-B	IO 5A-C	-	5A-B	IO 5A-C	-	-	-	-
Brånemark NP	NB	BM	6A-A	IO 6A-A	6A-A	IO 6A-A	-	6A-A	IO 6A-A	-	6A-A	IO 6A-A	-
Brånemark RP	NB	BM	6A-B	IO 6A-B	6A-B	IO 6A-B	-	6A-B	IO 6A-B	-	6A-B	IO 6A-B	-
Brånemark WP	NB	BM	6A-C	IO 6A-C	6A-C	IO 6A-C	-	6A-C	IO 6A-C	-	6A-C	IO 6A-C	-
Biomet External Hex 3.4	BIO	iii EXT	7A-A	IO 7A-A	7A-A	IO 7A-A	-	-	-	-	-	-	-
Biomet External Hex 4.1	BIO	iii EXT	7A-B	IO 7A-B	7A-B	IO 7A-B	-	-	-	-	-	-	-
Biomet External Hex 5.0	BIO	iii EXT	7A-B	IO7A-B	7A-B	IO7A-B	-	-	-	-	-	-	-
Biomet External Hex 6.0	BIO	iii EXT	7A-B	IO 7A-B	7A-B	IO 7A-B	-	-	-	-	-	-	-
Biomet Certain 3.4	BIO	iii CE	7B-A	IO 7B-A	7B-A	IO 7B-A	-	7B-A	IO 7B-A	-	-	-	-
Biomet Certain 4.1	BIO	iii CE	7B-B	IO 7B-B	7B-B	IO 7B-B	-	7B-B	IO 7B-B	-	-	-	-
Biomet Certain 5.0	BIO	iii CE	7B-B	IO 7B-B	7B-B	IO 7B-B	-	7B-B	IO 7B-B	-	-	-	-
Biomet Certain 6.0	BIO	iii CE	7B-B	IO 7B-B	7B-B	IO 7B-B	-	7B-B	IO 7B-B	-	-	-	-
Dentsply Xive D3.0	DS	XI	8A-A	IO 8A-A	8A-A	IO 8A-A	-	-	-	-	-	-	-
Dentsply Xive D3.4	DS	XI	8A-B	IO 8A-B	8A-B	IO 8A-B	-	-	-	-	-	-	-
Dentsply Xive D3.8	DS	XI	8A-C	IO 8A-C	8A-C	IO 8A-C	-	-	-	-	-	-	-
Dentsply Xive D4.5	DS	XI	8A-D	IO 8A-D	8A-D	IO 8A-D	-	-	-	-	-	-	-
Dentsply Xive D5.5	DS	XI	8A-D	IO 8A-D	8A-D	IO 8A-D	-	-	-	-	-	-	-
Dentsply Ankylos 3.5	DS	AN	-	-	-	IO 8B-A	IO 8B-A SA	-	-	-	-	-	-
Dentsply Ankylos 4.5	DS	AN	-	-	-	IO 8B-A	IO 8B-A SA	-	-	-	-	-	-
Dentsply Ankylos 5.5	DS	AN	-	-	-	IO 8B-A	IO 8B-A SA	-	-	-	-	-	-
Dentsply Ankylos 7.0	DS	AN	-	-	-	IO 8B-A	IO 8B-A SA	-	-	-	-	-	-
Dentsply Ankylos Balance Base	DS	AN-B	8C-A	IO 8C-A	-	-	-	8C-A	IO 8C-A	-	8C-A	IO 8C-A	-
Camlog 3.3	CL	SL	9A-A	IO 9A-A	9A-A	IO 9A-A	-	-	-	-	-	-	-
Camlog 3.8	CL	SL	9A-B	IO 9A-B	9A-B	IO 9A-B	-	-	-	-	-	-	-
Camlog 4.3	CL	SL	9A-C	IO 9A-C	9A-C	IO 9A-C	-	-	-	-	-	-	-
Camlog 5.0	CL	SL	9A-D	IO 9A-D	9A-D	IO 9A-D	-	-	-	-	-	-	-
Camlog 6.0	CL	SL	9A-D	IO 9A-D	9A-D	IO 9A-D	-	-	-	-	-	-	-